

**TECHSPEC® 10mm, Aluminum Coated, N-BK7 Right Angle Prism**



N-BK7 Right Angle Prisms

Stock **#32-331** ☐ In Stock

-

1

+

**C\$85.40**

ADD TO CART

Qty 1-5

C\$85.40

Qty 6+

C\$76.86

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Coating:**  
Aluminum with protective overcoat

**Substrate:** ☐  
[N-BK7](#)

**Surface Quality:**  
60-40

|                                                                                                                          |
|--------------------------------------------------------------------------------------------------------------------------|
| <b>Type:</b><br>Right Angle Prism                                                                                        |
| <b>Dimensional Tolerance (mm):</b><br>±0.1                                                                               |
| <b>Angle Tolerance (arcmin):</b><br>±2                                                                                   |
| <b>Bevel:</b><br>Protective bevel as needed                                                                              |
| <b>Length of Hypotenuse (mm):</b><br>14.10                                                                               |
| <b>Length of Legs (mm):</b><br>10.00                                                                                     |
| <b>Image Orientation:</b><br>Left-Handed                                                                                 |
| <b>Coating Specification:</b><br>Reflective Surfaces: R <sub>avg</sub> >85% FROM 400-700nm, @ 45° AOI                    |
| <b>Ray Deviation (°):</b><br>90                                                                                          |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                                               |
| <b>Surface Flatness (P-V):</b><br>λ/4                                                                                    |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>Hypotenuse: 0.3 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |