

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Specialty Lenses](#) / [Focusable Collimators](#)

[See all 19 Products in Family](#)

10mm Aperture, 25mm FL UV/VIS Fiber Refocusing Assembly



Fiber Refocusing Assembly

Stock **#88-186** ☐ In Stock

-

1

+

C\$434.00

ADD TO CART

Qty 1-10
C\$434.00
Qty 11+
C\$382.90
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
15.88

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Type:
Refocusing Assembly

Wavelength Range (nm):

190 - 1250
Aperture Size: 10.0
Focal Length FL (mm): 25.00
Housing Material: Anodized Aluminum
Length (mm): 16.38
Note: Compatible with #88-180 , #88-181 , #88-190 , & #88-191 Fiber Collimators
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View