

22.2mm Aperture, 51mm FL UV/VIS Fiber Refocusing Assembly



Fiber Refocusing Assembly

Stock **#17-574** ☐ In Stock

-

1

+

C\$861.00

ADD TO CART

Qty 1-10
C\$861.00
Qty 11+
C\$762.30
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 28.58
Substrate: ☐ Fused Silica (Corning 7980)
Type: Refocusing Assembly
Wavelength Range (nm):

190 - 1250
Aperture Size: 22.2
Focal Length FL (mm): 51.00
Housing Material: Anodized Aluminum
Length (mm): 25.40
Note: Compatible with #17-567 & #17-569 Fiber Collimators
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View