

TECHSPEC® 10mm Dia. Protected Gold, λ/4 Mirror



Stock **#45-600** ☐ In Stock

1

C\$91.00

ADD TO CART

Qty 1-5

C\$91.00

Qty 6+

C\$72.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
10.00

Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:

Commercial Polish
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 2.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant