

10mm Diameter 120 Grit Ground Glass Diffuser



Stock **#83-082** ☐ In Stock

- 1 +

C\$24.85

ADD TO CART

Qty 1-10
C\$24.85
Qty 11+
C\$21.35
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
10.00 ±0.25

Coating:
Uncoated

Edges:
Ground Edges

Grit: ☐
120

Substrate: Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Note: Sandblasted on first surface

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
