

TECHSPEC® 10mm H x 20mm L x 75mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#43-861** CLEARANCE ☐ In Stock

-

1

+

C\$106.33

ADD TO CART

Qty 1+

C\$106.33

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
75.00

Substrate: ☐
[N-BK7](#)

f/#:
7.5

Numerical Aperture NA:
0.07

Coating:
Uncoated

Type:	Cylinder Lens, Plano-Convex
Wavelength Range (nm):	350 - 2200
Back Focal Length BFL (mm):	73.72
Center Thickness CT (mm):	2.00
Center Thickness Tolerance (mm):	±0.1
Dimensional Tolerance (mm):	+0.0/-0.2
Dimensions (mm):	10.0 x 20.0
Edge Thickness ET (mm):	1.67
Focal Length Tolerance (%):	±3
Radius R ₁ (mm):	38.72
Surface Quality:	60-40
Tilt Tolerance (mm):	±0.1 over H
Wedge Tolerance (arcmin):	15.00

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View