

TECHSPEC® 10mm Length, C-Mount Extension Tube



Stock **#54-629** **8 In Stock**

- 1 + C\$46^{.55}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$46.55 each
Qty 5-9	C\$42.14 each
Qty 10-25	C\$39.06 each
Need More?	Request Quote

Product Downloads

General

Extension Tube **Type:**
Extension Tube (Fixed) **Function:**

Physical & Mechanical Properties

10.0 **Extension Length (mm):**

14.0	Total Length (mm):
22.0	Clear Aperture CA (mm):
30.0	Outer Diameter (mm):

Threading & Mounting

C-Mount	Thread Type:
---------	---------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

