

TECHSPEC®

10mm NIR, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock #47-123

In Stock

-

1

+

C\$320.60

ADD TO CART

Qty 1-5

C\$320.60

Qty 6+

C\$249.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

NIR
Coating Specification: R _{avg} <0.5% @ 720 - 1080nm
Construction: Cube
Dimensions (mm): 10.0 x 10.0 x 10.0 ±0.1
Reflection/Transmission Ratio (R/T): 50/50
Substrate:  N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 720 - 1080
[Ts-Tp]: <6%
Absolute Transmission (%): 45 ±10
Average Transmission (%): 45 ±5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
