

TECHSPEC[®] 10mm Length, T-Mount Extension Tube



Stock **#52-294** 20+ In Stock

-1+

C\$46^{.55}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$46.55 each
Qty 5-9	C\$42.14 each
Qty 10-25	C\$39.06 each
Need More?	Request Quote

Product Downloads

General	
Extension Tube	Type:
Extension Tube (Fixed)	Function:
Physical & Mechanical Properties	
10.0	Extension Length (mm):

13.45	Total Length (mm):
48.0	Outer Diameter (mm):
37.0	Clear Aperture CA (mm):

Threading & Mounting

T-Mount	Thread Type:
---------	--------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.