

10µm Aperture Diameter, Mounted, Precision Pinhole



10µm Aperture Diameter, Mounted, Precision Pinhole, #56-276

Stock **#56-276** ☐ In Stock



1



C\$119.00

ADD TO CART

Qty 1-5

C\$119.00

Qty 6+

C\$105.28

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:

Mounted

Outer Diameter (mm):

25 +0.4/-0.000

Construction:

Stainless Steel

Fixed Aperture Diameter (µm):

10
Thickness (mm): 0.01 Nominal
Aperture Tolerance (µm): ±1
Mount Thickness (mm): 1.25 ±0.05
Aperture Centration (µm): ±125

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

