

5/Pack, M3X0.5 X 3 SHSS-Soft



Stock **#58-630** 14 In Stock

-

1

+

C\$41<sup>.30</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | C\$41.30 each                 |
| Qty 10-24      | C\$37.17 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 247:                  |

# Product Details

- A Broad Selection of Sizes Available
- [Socket Head Set Screw Kits](#) Available
- [Allen Wrenches](#) Also Available
- Used in a Variety of Breadboard Configurations in Typical Lab Quantities.

## Technical Information

|         | Allen Wrench Stock No.  | Allen Wrench Hex Key Size | For Socket Head Cap | For Socket Head Set | For Button Head Cap |
|---------|-------------------------|---------------------------|---------------------|---------------------|---------------------|
| English | <a href="#">#58-639</a> | 0.028"                    | N/A                 | #0                  | N/A                 |
|         | <a href="#">#58-638</a> | 0.035"                    | N/A                 | #2                  | #0                  |
|         | <a href="#">#56-271</a> | 0.050"                    | #0                  | #4                  | #2                  |
|         | <a href="#">#58-637</a> | 1/16"                     | #1                  | #6                  | #3 & #4             |
|         | <a href="#">#56-270</a> | 1/64"                     | #2 & #3             | #8                  | #5 & #6             |
|         | <a href="#">#55-188</a> | 3/32"                     | #4 & #5             | #10                 | #8                  |
|         | <a href="#">#55-189</a> | 7/64"                     | #6                  | N/A                 | N/A                 |
|         | <a href="#">#03-662</a> | 1/8"                      | N/A                 | ¼"                  | #10                 |
|         | <a href="#">#55-190</a> | 9/64"                     | #8                  | N/A                 | N/A                 |
|         | <a href="#">#55-191</a> | 5/32"                     | #10 & #12           | 5/16"               | #12 & ¼"            |
|         | <a href="#">#55-192</a> | 3/16"                     | ¼"                  | 3/8"                | 5/16"               |
| Metric  | <a href="#">#58-636</a> | 0.9mm                     | N/A                 | M2                  | N/A                 |
|         | <a href="#">#55-452</a> | 1.5mm                     | M1.6 & M2           | M3                  | M2.5                |
|         | <a href="#">#57-445</a> | 2mm                       | M2.5 & M2.6         | M4                  | M3                  |
|         | <a href="#">#55-451</a> | 2.5mm                     | M3                  | M5                  | M4                  |
|         | <a href="#">#55-199</a> | 3mm                       | M4                  | M6                  | M5                  |
|         | <a href="#">#55-200</a> | 5mm                       | M6                  | M10                 | M8                  |