

10X DIN Semi-Plan, Finite Intl Standard Objective



Stock **#33-470** ☐ In Stock

-

1

+

C\$217.00

ADD TO CART

Qty 1+
C\$217.00

Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
546

Field of View (mm):
2

Focal Length FL (mm):
16.00

Length excluding Threads (mm):
35.00

Magnification:
10X

Maximum Diameter (mm): 25
Numerical Aperture NA: 0.25
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 160mm
Type: Semi-Plan
Depth of Field (µm): 17.45
Field of View, 18 Diameter Field Eyepiece (mm): 1.8
Operating Temperature (°C): +10 to +40
Operating Humidity: Max 85% at 35°C with no condensation
Working Distance (mm): 6.4
Weight (g): 51.2
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Field Number (mm): 20
Parfocal Length (mm): 41.4
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View