

10X ZEISS EC Epiplan Objective

See More by [ZEISS](#)



ZEISS EC Epiplan Objectives



Stock **#13-823** ☐ In Stock

-

1

+

C\$882.00

ADD TO CART

Qty 1+
C\$882.00

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Field of View (mm):
2.3

Focal Length FL (mm):
16.50

Model Number:

422040-9902-000
Length excluding Threads (mm): 34.00
Magnification: 10X
Maximum Diameter (mm): 30
Numerical Aperture NA: 0.25
Mounting Threads: M27 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 164.50mm
Type: Microscope Objective
Typical Applications: Fluorescence, BrightField, Differential Interference Contrast, Reflected Light DIC, DIC with circular polarized light
Resolving Power (µm): 1.1
Depth of Field (µm): 4.40
Operating Temperature (°C): +10 to +40
Operating Humidity: 75% at 35°C
Working Distance (mm): 11
Weight (g): 145
Wavelength Range (nm): 480 - 650
Style: Infinity Corrected
Manufacturer: ZEISS
Field Number (mm): 23
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View