

TECHSPEC® 1:1 with 14mm and 14mm EFL Achromats, 15mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#43-992** ☐ In Stock

1 **C\$255.50**

ADD TO CART

Qty 1-5

C\$255.50

Qty 6+

C\$204.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
9.5

Center Air Spacing (mm):
0.92

Substrate: ☐
[N-BAF10](#) / [N-SF5](#) / [N-BAF10](#) / [N-SF5](#)

Surface Quality:

40-20
Working f#: f/1.34
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Effective Focal Length EFL A (mm): 14.00
Effective Focal Length EFL B (mm): 14.00
Housing Diameter (mm): 15 +0.0/-0.10
Housing Length (mm): 21 ±0.2
Lens Edge Spacing at Mount (mm): 4
Magnification: 1:1
Object Distance (mm): 7.11
Image Distance (mm): 7.11
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
