

11.0" x 11.0", 19" Focal Length, Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock **#32-690** ☐ In Stock

-

1

+

C\$184.80

ADD TO CART

Qty 1-10

C\$184.80

Qty 11+

C\$163.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):

482.60

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.09
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 11.0 x 11.0
Dimensions (mm): 279.4 x 279.4
Effective Focal Length EFL (inches): 19.00
Effective Size (inches): 10.5 x 10.5
Groove Density (grooves/inch): 50.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View