

TECHSPEC® 11.2mm CA, 20mm FL, Mounted MgF₂ Coated Plano-Convex Lens



Mounted MgF₂ Coated Plano-Convex (PCX) Lenses



Stock **#12-916** CLEARANCE ☐ In Stock

1

C\$60.13

ADD TO CART

Qty 1+
C\$60.13
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
20.00

Substrate: ☐
[N-BK7](#)

f#:
1.67

Numerical Aperture NA: 0.30
Coating: MgF ₂ (400-700nm)
Type: Plano-Convex Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL from Housing (mm): 17.69
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 11.2
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Edge Thickness ET (mm): 1.58
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): 10.34
Surface Quality: 40-20
Lens Included: #49-887
Mount Included: #54-615
Mount Diameter (mm): 30.0
Extension Length (mm): 5.6
Total Length (mm): 9.6
Thread Type: C-Mount
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View