

1.2 OD M30.5 x 0.50, Machine Vision Absorptive ND Filter



Stock **#21-770** ☐ In Stock

-

1

+

C\$87.50

ADD TO CART

Qty 1-9
C\$87.50
Qty 10+
C\$83.72
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):

1.2

Clear Aperture CA (mm):

25.50

Filter Thread:

M30.5 x 0.50

Substrate:

☐ ND Filter Glass

Surface Quality: 40-20
Transmission (%): 6.25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
