

## 1.2 OD M46 x 0.75, Machine Vision Absorptive ND Filter



Stock **#21-651** ☐ In Stock

- 1 +

C\$94.50

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| C\$94.50                      |
| Qty 10+                       |
| C\$90.72                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

**Optical Density OD (Average):**  
1.2

**Clear Aperture CA (mm):**  
41.00

**Filter Thread:**  
M46 x0.75

**Substrate:** ☐  
ND Filter Glass

|                                                       |
|-------------------------------------------------------|
| <b>Surface Quality:</b><br>40-20                      |
| <b>Transmission (%):</b><br>6.25                      |
| <b>Type:</b><br>Mounted Imaging Filter                |
| <b>Blocking Wavelength Range (nm):</b><br>425 - 675   |
| <b>Mount Thickness (mm):</b><br>5.2                   |
| <b>Mount Thickness Including Threads (mm):</b><br>7.0 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---