

1.2 OD M58 x 0.75, Machine Vision Absorptive ND Filter



Stock **#21-736** ☐ In Stock

1

C\$94.50

ADD TO CART

Qty 1-9
C\$94.50
Qty 10+
C\$90.72
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
1.2

Clear Aperture CA (mm):
53.00

Filter Thread:
M58 x0.75

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 6.25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
