

TECHSPEC® 12.0mm Dia. x -18 FL, Uncoated, Plano-Concave Lens



TECHSPEC Uncoated Plano-Concave (PCV) Lenses



Stock **#48-335** ☐ In Stock

☐ [Other Coating Options](#)

1

C\$41.30

ADD TO CART

Qty 1-9

C\$41.30

Qty 10+

C\$37.10

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-18.00
Substrate: NSF11
f#: 1.5
Numerical Aperture NA: 0.33
Coating: Uncoated
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -19.95
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Edge Thickness ET (mm): 4.70
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R ₁ (mm): -14.12
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View