

**TECHSPEC® 12.5" Diameter x 75" FL Uncoated, Parabolic Mirror**



Stock #32-276-000 ☐ In Stock

1  **C\$4,011.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-2                       |
| C\$4,011.00                   |
| Qty 3+                        |
| C\$3,409.00                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Substrate: ☐ BOROFLOAT®☒ SUPREMAX®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy: λ/8

|                                                     |
|-----------------------------------------------------|
| <b>Diameter (inches):</b><br>12.5 +0.06/-0          |
| <b>Diameter (mm):</b><br>317.50 +1.5/-0             |
| <b>Effective Focal Length EFL (inches):</b><br>75.0 |
| <b>Effective Focal Length EFL (mm):</b><br>1,905.00 |
| <b>Radius of Curvature (mm):</b><br>3,810.00        |
| <b>Aperture (f/#):</b><br>f/6                       |
| <b>Coating:</b><br>Uncoated                         |
| <b>Coating Type:</b><br>Uncoated                    |
| <b>Back Surface:</b><br>Ground                      |
| <b>Clear Aperture CA (mm):</b><br>286               |
| <b>Edge Thickness ET (inches):</b><br>2.13          |
| <b>Edge Thickness ET (mm):</b><br>54.10             |
| <b>Type:</b><br>Parabolic Mirror                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |