

12.5 x 17.5mm, 30R/70T, Plate Beamsplitter



Stock **#45-315** ☐ In Stock

-

1

+

C\$65.80

ADD TO CART

Qty 1-9
C\$65.80
Qty 10+
C\$46.20
Volume Pricing
Request Quote

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR 1/λ MgF₂ @ 550nm

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 12.5 x 17.5
Edges: Cut
Reflection/Transmission Ratio (R/T): 30/70
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 1.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant