

TECHSPEC[®] 12.5mm Dia x 12.5mm FL 1064nm V-Coat, Cylinder Lens



Laser Line PCX Cylinder Lens

Stock #33-230 CLEARANCE ☐ In Stock

-

1

+

C\$55.93

ADD TO CART

Qty 1+

C\$55.93

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.50

Effective Focal Length EFL (mm):
12.50

Substrate: ☐
[N-BK7](#)

f#:
1.00

Numerical Aperture NA:
0.50

Coating: Laser V-Coat (1064nm)
Type: Cylinder Lens, Plano-Convex
Back Focal Length BFL (mm): 7.57
Center Thickness CT (mm): 7.48
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} <0.25% @ 1064nm
Design Wavelength DWL (nm): 1064
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 2.72
Focal Length Tolerance (%): ±3
Note: Coating: 1064nm V-Coat
Radius R₁ (mm): 6.48
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View