

TECHSPEC® 12.5mm Dia. x 3mm Thick, 3-5µm AR Coating, Ge Window



Germanium (Ge) Windows

Stock **#89-561** ☐ In Stock

-

1

+

C\$438.20

ADD TO CART

Qty 1-10

C\$438.20

Qty 11+

C\$394.45

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
90.00

Clear Aperture CA (mm):
11.25

Diameter (mm): 12.50 +0.0/-0.1
Thickness (mm): 3.00 ±0.1
Coating: BBAR (3000-5000nm)
Coating Specification: R _{avg} <3% @ 3 - 5µm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.1
Density (g/cm³): 5.33
Edges: Fine Ground
Index of Refraction n_d: 4.002 @ 11µm
Knoop Hardness (kg/mm²): 780
Parallelism (arcmin): <1
Poisson's Ratio: 0.28
Substrate: Germanium (Ge)
Surface Flatness (P-V): λ/10 @ 10.6µm
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 3000 - 5000
Young's Modulus (GPa): 102.7

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant