

TECHSPEC® 12.5mm Dia x -100mm FL VIS-NIR Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#69-836** ☐ In Stock

1

C\$114.80

ADD TO CART

Qty 1-5

C\$114.80

Qty 6+

C\$91.70

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Effective Focal Length EFL (mm):
-100.00

Substrate: ☐
[N-BK7](#)

f/#: 8.00
Numerical Aperture NA: 0.06
Coating: VIS-NIR (400-1000nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -101.32
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 2.38
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -51.68
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant