

TECHSPEC® 12.5mm Dia x -25mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#47-749** ☐ In Stock

-

1

+

C\$86.80

ADD TO CART

Qty 1-5

C\$86.80

Qty 6+

C\$69.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Effective Focal Length EFL (mm):
-25.00

Substrate: ☐
[N-BK7](#)

f/#: 2.00
Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -26.32
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 3.61
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -12.92
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View