

12.5mm Diameter, Yellow Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#52-542** ☐ In Stock



1



C\$30.80

ADD TO CART

Qty 1-24

C\$30.80

Qty 25+

C\$27.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0

Cut-On Wavelength (nm):
520.00

Substrate:  BOROFLOAT®
Operating Temperature (°C): <100
Coating: Subtractive Color
Color: Yellow
Surface Quality: 80-50
Thickness (mm): 2.00 Nominal
Type: Dichroic Filter
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥85
Cut-On Wavelength Tolerance (µm): 0.015
Coating Specification: T _{avg} <1.0% @ 400 - 475nm T _{avg} >80% @ 550 - 750nm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant