

TECHSPEC[®] 125mm, Side Drive, Standard Top, Metric Micrometer Stage



125mm Micrometer Drive Stage

Stock #66-460 ☐ In Stock

-

1

+

C\$812.00

ADD TO CART

Qty 1-2

C\$812.00

Qty 3+

C\$708.26

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:

Linear (X)

Guide System:

Crossed Roller Bearing

Type of Drive:

Metric Micrometer

Drive Orientation:

Side Drive
Type: Metric
Stage Size (mm): 125 x 125
Travel (mm): 25
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 20
Mounting Threads: (21) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
