

TECHSPEC® 12.5mm, Uncoated, Rhomboid Prism



Stock **#49-418** ☐ In Stock

-

1

+

C\$234.50

ADD TO CART

Qty 1-5
C\$234.50
Qty 6+
C\$187.60
Volume Pricing
Request Quote

Get Product Downloads



Length (mm):
12.50

Coating:
Uncoated

Angle Tolerance (arcsec):
±5

Beam Deviation (arcsec):

±30
Dimensional Tolerance (mm): ±0.1
Image Orientation: Beam Deviation
Ray Deviation (°): 0.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Rhomboid Prism
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View