


SCHOTT AS87ECO, 12.7 x 127mm, 0.1mm Thick, Ultra-Thin Window

See More by [SCHOTT Optical Components](#)



Stock **#12-312** CLEARANCE ☐ In Stock

1

C\$53.20

ADD TO CART

Qty 1-10

C\$53.20

Qty 11+

C\$42.70

Volume Pricing

[Request Quote](#)

Get Product Downloads

Abbe Number (v_d):
59.5

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

11.43 x 114.30
Dimensions (mm): 12.70 x 127.00
Thickness (mm): 0.10 ±0.01
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.7
Density (g/cm³): 2.46
Index of Refraction n_d: 1.504
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.216
Substrate: AS 87 ECO
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 200 - 3200
Young's Modulus (GPa): 73.3
Length (mm): 127.00
Width (mm): 12.70

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant