

[All Products](#) / [Optics](#) / [Prisms](#) / [Retroreflection Prisms](#) / [Hollow Retroreflectors](#)

[See all 44 Products in Family](#)

127mm Clear Aperture, 30 Arcsec, Aluminum Retroreflector



Stock **#49-673** CLEARANCE ☐ In Stock

- 1 + **C\$3,787.00**

ADD TO CART

Qty 1+
C\$3,787.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec): 30.00
Clear Aperture CA (mm): 127.0
Coating: Enhanced Aluminum (450-650nm)
Diameter (mm): 166.70
Exiting Wavefront Accuracy: 18.0λ

Substrate:  BOROFLOAT®
Surface Quality: 80-50
Mounting Threads: (7) ¼-20, (6) M6 x 1.0
Type: Retroreflector
Dimensional Tolerance (mm): ±1.6
Image Orientation: Left-Handed
Ray Deviation (°): 180
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View