

12.7mm, ISP Optics Germanium Equilateral Prism | GE-EP-12

See More by [ISP Optics](#)



Stock #19-711 ☒ In Stock

⊖

1

⊕

C\$1,953.00

ADD TO CART

Qty 1-5

C\$1,953.00

Qty 6+

C\$1,562.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

Germanium (Ge)

Surface Quality:

60-40

Type: Equilateral Prism
Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85
Length of Hypotenuse (mm): 12.70
Length of Legs (mm): 12.70
Wavelength Range (nm): 2000 - 14000
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 2λ
Model Number: ZC-EP-12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View