

TECHSPEC®

12.7mm H x 12.7mm L x 100mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #35-022 ☐ In Stock

-

1

+

C\$86.80

ADD TO CART

Qty 1-5

C\$86.80

Qty 6+

C\$69.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate: ☐
[N-BK7](#)

f/#:
7.8740157480315

Numerical Aperture NA: 0.06
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 98.02
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 2.61
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.68
Surface Quality: 60-40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View