



12.7mm H x 12.7mm L x 150mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#35-023** ☐ In Stock

- 1 +

C\$86.80

ADD TO CART

Qty 1-5
C\$86.80
Qty 6+
C\$69.30
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
150.00

Substrate: ☐
[N-BK7](#)

f/#:
11.8110236220472

Numerical Aperture NA: 0.04
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 148.25
Center Thickness CT (mm): 2.65
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 2.39
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 77.52
Surface Quality: 60-40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View