

TECHSPEC® 12.7mm H x 12.7mm L x 25mm FL VIS 0°, Illumination Grade PCX Cylinder Lens



Stock **#36-209** ☐ In Stock

1 **C\$114.80**

ADD TO CART

Qty 1-5
C\$114.80
Qty 6+
C\$91.70
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
25.00

Substrate: ☐
[N-BK7](#)

f/#:
1.96850393700787

Numerical Aperture NA:

0.25
Coating: MS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 23.02
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 1.33
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.92
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant