

[See all 11 Products in Family](#)

12.5/12.7mm Optic Dia., X-Y Translating Optic Mount



5 Axes Optical Mount



Stock #62-955 **7 In Stock**

⊖ 1 ⊕ C\$365⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	C\$365.40 each
Qty 5-9	C\$347.34 each
Qty 10+	C\$310.80 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Linear (XY) **Type:**

Circular **Type of Optics:**

Physical & Mechanical Properties

10.0	Clear Aperture CA (mm):
64.0	Outer Diameter (mm):
20.00	Thickness (mm):
±1.5 in X and Y	Travel (mm):
180	Weight (g):
Black Anodized Aluminum	Construction:

Threading & Mounting

12.5 - 12.7	Size of Compatible Optics (mm):
15.0 (Max)	Thickness of Compatible Optics (mm):
M6 x 1.0	Compatible Post:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

Technical Information

