

TECHSPEC® 12mm Diameter x -48 FL, VIS 0°, Inked, Plano-Concave Lens



Stock **#47-907-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 +

C\$72.80

ADD TO CART

Qty 1-9
C\$72.80
Qty 10+
C\$65.45
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.00 ±0.025

Effective Focal Length EFL (mm):
-48.00

Substrate: N-BK7
f/#: 4.00
Numerical Aperture NA: 0.13
Coating: VS 0° (425-675nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -50.31
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Coating Specification: R_{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 4.12
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -24.81
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View