

98mm Max. Aperture, Iris Diaphragm



Stock **#32-611** ☐ In Stock

-

1

+

C\$555.80

ADD TO CART

Qty 1-4
C\$555.80
Qty 5+
C\$490.84
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
5.0

Maximum Aperture (mm):
98.0

Outer Diameter (mm):
130.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 20.00
Number of Leaves: 20.00
Thickness (mm): 12.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)
