

13mm Travel, 0.01mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#33-727** 1 In Stock

-

1

+

C\$127⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$127.40 each
Qty 10-24	C\$114.66 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Mitutoyo	Manufacturer:
Physical & Mechanical Properties	
13	Travel (mm):
	Graduation (mm):

0.01	
	Stem Diameter (mm):
9.5	
	Stem/Spindle:
Plain/Spherical	
	Stem Length (mm):
9.5	
	Spindle Diameter (mm):
5	
	Min. Spindle Length (mm):
15.5	
	Max. Diameter (mm):
13	
	Overall Length (mm):
62	

Hardware & Interface Connectivity

	Type of Drive:
Metric Micrometer	

Regulatory Compliance

	RoHS 2015:
Exempt	
	Certificate of Conformance:
View	
	REACH 241:
Contains SVHC(s)	

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.
- Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

