

13mm Travel, Fine Screw, Solid-Top Ball Bearing Stage



32mm/1.25" Center drive stage and its X-Y-Z configuration

Stock **#56-358** ☐ In Stock



1



C\$547.40

ADD TO CART

Qty 1+

C\$547.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Fine Screw (64 Pitch)

Drive Orientation:
Center Drive

Type:
Metric

Stage Size (mm): 31.8 x32.5
Travel (mm): 12.7
Construction: Aluminium Stage
Graduation (mm): No
Height (mm): 12.7
Load Capacity, Normal (kg): 3
Load Capacity, T_a (kg): 4.5
Note: Solid Top
Straight Line Accuracy (µm): 2 per 25mm of travel
Weight (kg): 0.078
Thrust Capacity, T_a (kg): 4.5
Thrust Capacity, T_b (kg): 1.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View