

## 140mm Length, Adjustable Laser Holder



#56-332, #56-333

Stock **#56-332** **5 In Stock**

- 1 + C\$525<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	C\$525.00 each
Qty 5-25	C\$464.10 each
Qty 26-49	C\$427.42 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Adjustable - Tilt **Type:**  
Cylindrical Tube **Type of Optics:**

### Physical & Mechanical Properties

140.00 **Length (mm):**

740 **Weight (g):**

**Construction:**  
Black Anodized Aluminum

**Twin Ring Mount Adjustment Screw Pitch (mm):**  
0.5

**Tilt Angle (°):**  
±4

### Threading & Mounting

**Size of Compatible Optics (mm):**  
20.0 - 55.0

**Compatible Post:**  
M6 x 1.0

### Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Contains SVHC\(s\)](#)

## Product Details

- Twin Ring Mount Design
- Fixed and Adjustable Versions
- Ideal for He-Ne Lasers
- [Posts](#) and [Post Holders](#) Required for Mounting

Designed for [Helium-Neon Lasers](#), this mount is ideal for any optical tube assembly. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

Mounting hole is M6 x 1.0

## Technical Information

