

140mm Length, Adjustable Laser Holder



#56-332, #56-333

Stock **#56-332** 5 In Stock

-

1

+

C\$525⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$525.00 each
Qty 5-25	C\$464.10 each
Qty 26-49	C\$427.42 each
Need More?	Request Quote

Product Downloads

General	
Adjustable - Tilt	Type:
Cylindrical Tube	Type of Optics:
Physical & Mechanical Properties	
140.00	Length (mm):

740	Weight (g):
Black Anodized Aluminum	Construction:
Twin Ring Mount Adjustment Screw Pitch (mm): 0.5	
±4	Tilt Angle (°):

Threading & Mounting

20.0 - 55.0	Size of Compatible Optics (mm):
M6 x 1.0	Compatible Post:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- Twin Ring Mount Design
 - Fixed and Adjustable Versions
 - Ideal for He-Ne Lasers
 - [Posts](#) and [Post Holders](#) Required for Mounting
- Designed for [Helium-Neon Lasers](#), this mount is ideal for any optical tube assembly. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.
- Mounting hole is M6 x 1.0

Technical Information

