

14.0" Diameter, 24" Focal Length, Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock **#43-020** ☐ In Stock

-

1

+

C\$357.00

ADD TO CART

Qty 1-10

C\$357.00

Qty 11+

C\$308.70

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
355.60

Effective Focal Length EFL (mm):
609.60

Substrate: ☐
Acrylic

Coating:

Uncoated
Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.11
Diameter (inches): 14.0
Dimensional Tolerance (inches): ±0.05
Effective Diameter (inches): 12.9
Effective Focal Length EFL (inches): 24.00
Groove Density (grooves/inch): 200.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View