

150 x 150mm 220 Grit Ground Glass Diffuser



Stock **#47-951** ☐ In Stock

- 1 +

C\$89.60

ADD TO CART

Qty 1-10
C\$89.60
Qty 11+
C\$80.50
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Uncoated

Dimensional Tolerance (mm):
±0.76

Dimensions (mm):
150.00 x 150.00

Edges:
Seamed Edges

Grit: 220
Substrate: Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 150.00
Note: Sandblasted on first surface
Length (mm): 150.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant