

TECHSPEC<sup>®</sup> 15mm Dia Enhanced Aluminum, 4-6λ Mirror



Stock **#32-943** ☐ In Stock

-

1

+

C\$33.60

ADD TO CART

Qty 1-5

C\$33.60

Qty 6+

C\$25.90

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):  
15.00 ±0.25

Surface Flatness (P-V):  
4 - 6λ

Substrate: ☐  
Float Glass

Surface Quality:  
60-40

|                                                                                                    |
|----------------------------------------------------------------------------------------------------|
| <b>Dimensional Tolerance (mm):</b><br>±0.25                                                        |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≥95% @450 - 650nm @45°                           |
| <b>Coating:</b><br>Enhanced Aluminum (450-650nm)                                                   |
| <b>Coating Type:</b><br>Metal                                                                      |
| <b>Clear Aperture CA (mm):</b><br>14.00                                                            |
| <b>Edges:</b><br>Ground, 0.5mm Maximum Edge Chip                                                   |
| <b>Thickness (mm):</b><br>3.00 nominal                                                             |
| <b>Type:</b><br>Flat Mirror                                                                        |
| <b>Wavelength Range (nm):</b><br>450 - 650                                                         |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>0.2 J/cm <sup>2</sup> @532nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |