

15mm Diameter Unmounted, Linear Glass Polarizing Filter



Stock **#54-925** ☐ In Stock

1

C\$57.40

ADD TO CART

Qty 1-5
C\$57.40
Qty 6+
C\$44.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00

Extinction Ratio:
100:1

Substrate: ☐
Polymer Film on [B270](#)

Operating Temperature (°C):

-15 to +70
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): Single: ~30
Type: Linear Polarizer
Parallelism (arcmin): <3
Dimensional Tolerance (mm): +0.0/-0.2
Bevel: Protective bevel as needed
Construction: Dichroic Polarizing Film on Glass
Edges: Cut
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): 4 - 6λ
Polarization Efficiency (%): 95

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View