

15mm Diameter UV Fused Silica Ground Glass Optical Diffuser



Stock **#49-156** ☐ In Stock

1 **C\$73.50**

ADD TO CART

Qty 1-10
C\$73.50
Qty 11+
C\$58.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 ±0.25

Grit: ☐
220

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Thickness (mm):

1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant

