


TECHSPEC®

15mm Minor Axis Uncoated, Fused Silica Brewster Window



Stock #65-825 CLEARANCE CONTACT US

-

1

+

C\$88.13

ADD TO CART

Qty 1+

C\$88.13

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
13.50 x23.88

Thickness (mm):
2.00 ±0.20

Coating:
Uncoated

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
0.52 (+5 to +35°C)
0.57 (0 to +200°C)
0.48 (-100 to +200°C)

Design Wavelength DWL (nm): 632.8
Edges: Fine Ground
Index of Refraction n_d: 1.458
Major Axis (mm): 26.53
Minor Axis (mm): 15.00 +0.00/-0.25
Parallelism (arcsec): ≤10
Substrate: Fused Silica (Coming 7980)
Surface Quality: 10-5
Transmitted Wavefront, P-V: λ/10
Type: Linear Polarizer
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Construction: Brewster Window

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View