

TECHSPEC®

15mm NIR I Hypotenuse, BBAR Right Angle Prism



Broadband Anti-Reflection Coated Hypotenuse Prism

Stock #34-408 ☒ In Stock



1



C\$157.50

ADD TO CART

Qty 1-5

C\$157.50

Qty 6+

C\$126.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Beam Deviation (arcsec):
±15

Coating:
NIR I (600-1050nm)

Substrate: ☐
[N-BK7](#)

Surface Quality: 40-20
Type: Right Angle Prism
Dimensional Tolerance (mm): +0/-0.1
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 21.20
Length of Legs (mm): 15.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/8

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant