

TECHSPEC®

15mm Uncoated Ultra Precision UV Fused Silica Right Angle Prism



Stock #35-904 ☐ In Stock



1



C\$411.60

ADD TO CART

Qty 1-5

C\$411.60

Qty 6+

C\$370.44

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Uncoated

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality:

20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 21.20
Length of Legs (mm): 15.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/20

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View